



1 100% PU

2 resistanc

3

4

3.5

6 40°C

7 REACH ROHS EN71-3 6 P



Finehope 2002 100 41 32. The 7000 1000







## 1. [Blank] Finehope [Blank] [Blank] [Blank]

1. [Blank] [Blank] [Blank] [Blank] [Blank] [Blank]
2. [Blank] [Blank] [Blank] [Blank] [Blank] [Blank] [Blank] [Blank]
3. Finehope [Blank] [Blank] [Blank] [Blank] [Blank] [Blank] [Blank] [Blank] [Blank] [Blank] [Blank] [Blank]
4. [Blank] [Blank] [Blank] [Blank]
5. [Blank] [Blank] [Blank] [Blank] [Blank]
6. [Blank] [Blank] [Blank] [Blank] [Blank] [Blank] [Blank] [Blank]
7. Finehope [Blank] [Blank] [Blank] [Blank] [Blank] [Blank] [Blank] [Blank] [Blank] [Blank]

## 2. [Blank] Finehope [Blank] [Blank] [Blank] [Blank] [Blank]

1. [Blank] [Blank] [Blank] [Blank] [Blank] [Blank] APQP [Blank]
2. Finehope [Blank] [Blank] [Blank] [Blank] [Blank] [Blank]
3. [Blank] [Blank] [Blank] [Blank] [Blank] [Blank]
4. [Blank] [Blank] [Blank] [Blank] [Blank] [Blank] [Blank] [Blank]
5. [Blank] [Blank] [Blank] [Blank] [Blank] [Blank] [Blank] [Blank]

## 3. [Blank] Finehope [Blank] [Blank] [Blank] [Blank] [Blank] [Blank]

1. [Blank] [Blank] [Blank] [Blank] [Blank]
2. [Blank] [Blank]
3. [Blank] [Blank] [Blank] [Blank] [Blank] [Blank] [Blank]
4. [Blank] [Blank] [Blank] [Blank] [Blank]

## 4. [Blank] [Blank] [Blank] Finehope [Blank]

Finehope [Blank] [Blank] [Blank] [Blank] [Blank] [Blank] [Blank] [Blank] R& [Blank]; [Blank] [Blank] [Blank] [Blank] [Blank] [Blank] [Blank] [Blank] [Blank] [Blank] [Blank] [Blank] CAT [Blank] [Blank]  
 [Blank] [Blank] TVH [Blank] GGP [Blank] [Blank] 12 [Blank] [Blank] [Blank] [Blank] [Blank] [Blank] [Blank] [Blank] [Blank] [Blank] R& [Blank] [Blank]; [Blank] [Blank] [Blank] [Blank] [Blank] [Blank] [Blank]

