



REACH
SVHC  **RoHS** SGS



REACH
SVHC  **RoHS** SGS



REACH
SVHC  **RoHS** SGS



REACH
SVHC  **RoHS** SGS



Finehope地毯 吸水性能测试

Micro Test

1

测试目的

前言

居家和办公室生长点极为潮湿、脏乱的环境下，如果地毯产品选用吸水性材料，在清洁工作中，经常拖家带口，甚至用脏污水飞溅地毯表面和底部，进而可能滋生霉菌，使得地毯内部沾染颗粒物质沉积成菌，这些环境因素，因此会使得整发霉滋生。

由于霉菌和细菌的滋生是检测深的环境造成的，因此我们在设计地毯和消费者选择地毯产品时应选择吸水性材料并定期清洁。

Finehope公司生产的地毯产品均选择聚酯纤维高吸水性纤维或聚氨酯原料，能够保持广大客户中霉菌的比别计更和更有竞争力的产品。



Micro Test

2

测试目的

- 按照ISO 10661:2019 (ISO 10661:2019) 标准进行地毯吸水性能测试。
测试方法：将地毯样品放入水中，测量其吸水性能。
测试条件：室温（20±2℃），相对湿度（50±5%）。
- 测试地毯吸水性能。
测试方法：将地毯样品放入水中，测量其吸水性能。
测试条件：室温（20±2℃），相对湿度（50±5%）。
- 测试地毯吸水性能。
测试方法：将地毯样品放入水中，测量其吸水性能。
测试条件：室温（20±2℃），相对湿度（50±5%）。

Micro Test

3

测试目的

- 按照ISO 10661:2019 (ISO 10661:2019) 标准进行地毯吸水性能测试。
测试方法：将地毯样品放入水中，测量其吸水性能。
测试条件：室温（20±2℃），相对湿度（50±5%）。
- 测试地毯吸水性能。
测试方法：将地毯样品放入水中，测量其吸水性能。
测试条件：室温（20±2℃），相对湿度（50±5%）。
- 测试地毯吸水性能。
测试方法：将地毯样品放入水中，测量其吸水性能。
测试条件：室温（20±2℃），相对湿度（50±5%）。



Micro Test

4

测试过程

- 测试过程准备
1. 将地毯样品放入水中，测量其吸水性能。
2. 测试地毯吸水性能。
3. 测试地毯吸水性能。
- 测试过程准备
1. 将地毯样品放入水中，测量其吸水性能。
2. 测试地毯吸水性能。
3. 测试地毯吸水性能。



Micro Test

5

测试过程

- 测试过程准备
1. 将地毯样品放入水中，测量其吸水性能。
2. 测试地毯吸水性能。
3. 测试地毯吸水性能。



Micro Test

6

测试过程

- 测试过程准备
1. 将地毯样品放入水中，测量其吸水性能。
2. 测试地毯吸水性能。
3. 测试地毯吸水性能。



Micro Test

7

测试过程

- 测试过程准备
1. 将地毯样品放入水中，测量其吸水性能。
2. 测试地毯吸水性能。
3. 测试地毯吸水性能。



Micro Test

8

测试过程

- 测试过程准备
1. 将地毯样品放入水中，测量其吸水性能。
2. 测试地毯吸水性能。
3. 测试地毯吸水性能。




Micro Test

9

测试分析

Finehope地毯吸水性能测试结果表明，Finehope地毯吸水性能优异，能够有效防止霉菌滋生，保障室内空气质量。



Micro Test

10

First, the product description

1. Features

Polyurethane no pattern mats Chinese suppliers, PU foam anti-fatigue mats Chinese factory, a model customized PU mats made in China, polyurethane mats

Since a skin foam characteristics:

1. Low density, light weight, no smell, the surface texture of leather, one piece no difference.
2. The high impact resistance, wear resistance, permanently elastic
3. waterproof, crack, anti-UV, anti-distortion, anti-aging;
4. Surface easy to color, easy to color the whole, are environmentally friendly products;
5. hardness with customer requirements modulation;
6. Can be made into any shape, it can be placed in reinforcing filler, light weight, easy to install;

2, the product uses

Since a soft leather products are widely used:

1. Automotive: bumper, steering wheel, armrest mats, car head cushions, shift lever, fenders, overcast flow plate, the instrument panel, air filter, bicycle seat, tractors, off-road vehicles cushion, reaction injection molding products Wait;
2. sports equipment: fitness equipment cushion, backrest, kneeling pads, grips, pedals, bicycle saddles, sports kneepad and so on;
3. Medical devices: one piece dental chairs, surgical table tops edge, hanging racks, wheelchair armrests;
4. Household items: armrest mats, chair legs, decorative items;
5. Other Uses: toys, packaging;

Second, with regard us

1. Introduction

- We are a leading manufacture of molded polyurethane products manufacturer, was established in 2002. Our products are mainly exported to European and US markets.
- We have a professional production of polyurethane products top-quality requirements for the goal. The main reason customers choose our fancy our broad R & D capabilities and with international brand companies and ensure long-term experience with shipping quality.
- Division I after the Swiss SGS ISO9001-2008 certification, in accordance with TS16949 system for quality control. Lean is we have been pursuing the goal to reduce waste, create additional value, sustained commitment to help our customers control costs and create additional value.



2, our brand customers

Located in various regions and industries the Americas, Europe, Asia welcome your visit, thank you!



3, our advantage

A. Quality management through the company ISO9001, ISO / TS 16949 quality management system continued to promote, maintain and regularly reviewed to ensure their full, appropriate and effective operation;

ISO / TS 16949 five core tools: effective use of APQP, FMEA, MSA, SPC, PPAP, so that our quality control and overall management level have been greatly improved, and ultimately to meet customer requirements.

B. materials research and development of polyurethane material has a professional R & D team has been put into products, including MDI, TDI, HDI, and PPDI and other polyether, polyester systems formula, covering all polyurethane systems formulations.

C. improved equipment for production equipment has the ability to self-improvement and self-designed research Jidoka mold fixture, lean from Dong line.

D. Toyota's lean production using TPS lean management model to improve production efficiency, reduce waste and reduce costs.



• PU Foaming Equipment
PU(聚氨酯) 发泡设备



4, our production

- Has PU industry's most advanced production equipment, including KraussMaffei machines and other production

materials of different PU products of high / low pressure perfusion machines;

- automated assembly line operations, including perfusion lines, painting lines, polishing lines, since shaken mold lines.
- have independent mold design, production, the ability to innovate, and a wealth of experience in the design and processing of metal, plastic and other parts of the PU;



5, our testing equipment

- FINEHOPE PU material has a range of testing equipment, and dedicated quality assurance system and quality control engineers.
- FINEHOPE will carry out the testing product analysis, mechanical analysis products and materials, and ultimately develop a test product. Thereby reducing the quality standards disputes between customers and manufacturers.





6, we certificates

- FINEHOPE as Huaqiao University, Xiamen University and the polyurethane product research and postgraduate training base station.
- FINEHOPE domestic high-tech enterprises, with a number of domestic and foreign patents polyurethane intellectual invention.
- FINEHOPE passed ISO9001 certification, Alibaba, Alibaba is also a boutique company Prudential enterprises.



Third, FAQ

1) Why did you choose FINEHOPE

FINEHOPE is China's most professional manufacturer of PU, has a professional R & D team, advanced PU production equipment, professional testing equipment and perfect quality management system. Division I and CAT, FIAT, TVH, GGP and other famous enterprises have 12 years of experience of cooperation. Division I provide them with one-stop service from the production and customization to meet their needs.

2) Select FINEHOPE benefits

Reduce your time, reduce personal problems, reduce costs (explicit and implicit costs).

3) the product delivery cycle

Upon receipt of the deposit and the completion of 30 days to complete mold production, preparation and equipment without queuing period 10 days (depending on order quantity).

4) Product of transport

Qiyun, shipping, air transport (FedEx / UPS), depending on customer requirements.

5) How to track goods transportation

If the ocean bill of lading number will be provided to the customer, if it is air transport will provide fast waybill number.

6) How good product quality control

Quality first, to provide customers with high quality products is our mission. A professional team from beginning to end, good product quality control:

- All the raw materials, parts prior to production must undergo a rigorous inspection;
- All workers must undergo pre-production formal training;
- All products must pass strict control and inspection in the production process;
- All products must be checked before shipping again.

Fourth, contact us



Tel: +86-592-6661766

Email: feiyan@finehope.com

For more information, please contact us. I am Feiyan Zeng, welcome your visit, thank you!

Phone: + 86-592-6661766

Fax: + 86-592-6282029

Miss Zeng Email: feiyan@finehope.com

English Web site: www.finehope.com

Chinese Web site: [http: //finehope.1688.com/](http://finehope.1688.com/)